
## Neonatal Ventilator Circuit







## Single Heated wire circuits for neonate & infants

- Compatible with F&P devices
- Comes with autofeed humidification chamber
- Can be used for all ventilators.
- For SLE 2000/4000/5000 ask for connector
- For babylog 8000 use component e from the component pack.
- For Maquet ventilators use HME filter.

## **Dual Heated wire circuits for neonate & infants**

- Compatible with F&P devices
- Comes with autofeed humidification chamber
- Can be used for all ventilators.
- For SLE 2000/4000/5000 ask for connector
- For babylog 8000 use component e from the component pack.
- For Maquet ventilators use HME filter.





## **Dual water trap circuits for neonate & infants**

- Compatible with F&P devices
- Comes with autofeed humidification chamber
- Can be used for all ventilators.
- For SLE 2000/4000/5000 ask for connector
- For babylog 8000 use component e from the component pack.
- For Maquet ventilators use HME filter.